



LICO Electronics GmbH A-2320 Kledering +43 1 706 43 00 office@lico.at







Original BONKOTE





BON102 = BR102 + CA102

Over all Length: BON102 approx. 170 mm the Printed Version scale is a bit smaller than 1:1







BONPEN, Japanese Precision, an Art on its own!

These handy Bon Pens allow for very accurate flux dispensing on the work area, while eliminating dripping and flooding, making it irreplaceable for every SMD-workplace

BONPEN-Materials: PP, PE, Nylon.


BONPEN is Suitable for: Fluxes, Alcohol, Fluoric Lube,

Primers, Flux inhibitors, Water

Available again: BON-102A set,

The Set contains 1 pc of all 6 different BON-102

(except BON-102S)



The LICO-Superscope, only available as well checked & refurbished pre-owned.

This is one of the smartest purchase you can make, * supply as long as stock lasts.

Microscope with 14" Display

Using this unique solution the operator can stop leaning over objects. Neck and backpain is a thing of the past!

The Super Scope offers a distortion-free Zoom-range of 4X - 40X (with optional Aux-lens can be reached 8X - 80X, as far as lens is available. A big working distance lens to object allows a convenient working depth on the objekt.

Including a LED light source with dimmer. The brightness can be regulated step-free. Optionally other light sources are available.

A large 14" high-resolution display from SONY Medical allows a very convenient inspection and work under the microscope.

A PAL-Video-output for Framegrabbers available on the PC-market rounds up the universal use of the versatile Microscope. Sliding arm and heavy stand-base is included.







www.bonkote.eu

Flux-Pens

The Packaging:

BON-102A - Set of 6 pcs



BON-102AS - Set of 7 pcs









日本ホンコート株

Flux-Pens

The Original-Bonkote Packaging

BONPEN & Spare-tips: Packages of 5 pcs each





LICO

Use only Original-Bonkote-parts to ensure the function and exclude handling and operation faults!
Please mind the user-manual!
(Manual.pdf) @ www.bonkote.eu!!!





LICO

www.bonkote.eu

The Bonkote Fine Cleaner

Are you using wet sponges or metal sponges to clean your soldering tips?

It is proven that such temperature shocks slowely but surely crack the coating surface of soldering tips. The temperature drop can be even 50 - 100°C And such circumstance can lead into instable soldering temperature. And finally such temperature shocks reduces the life expectance of soldering tips remarkably.

Metal sponges scratch the fine surface of soldering tips which also reduces the life expectance.

Bonkote round stainless steel bars and the smooth high temperature rubber **can save considerably** on your soldering tip life by avoiding scratches and high temperature drops.





The Fine-Cleaner consists out of a High temperature rubber part and a Magnet



This Magnet can be fixed at the bottom of the Cleaner



Strong residues can be pre-cleaned or cleaned at the rounded stainlessbars.



Simple residues can be cleaned off the tip at the rubber lip

Types:

Model	Inner Diameter	Outer Diameter	Weight
B-250	25 mm	50x22 mm	65 g
B-500	50 mm	87x30 mm	185 g

Materialies: Magnetic plate, High temperature-rubber, rounded stainless steel bars

SEE SIMPLY BETTER



EYESTRAIN REJECT

We have the right magnifier to improve your vision.



www.eurolupe.com

LICO Electronics GmbH, A-2320 Kledering LICO Hungaria Kft, H-2030 Erd

LICO Mecatronic, RO-540526 Targu-Mures +43 1 706 43 00 office@lico.at

MECHATRONIK

ELEKTRONIK UND

ELEKTROMASCHINENBA

HEISTERBETRIEB

Your personal Distributor



BONKOTE & LICO have various brands, marks and patents pending, Typing & printing errors cannot be excluded. Technical changes possible anytime without any further announcement